


REFRIGERATED DROP-INS

Refrigerated Short Side Drop-Ins

- Thick polyurethane foam insulation
- 3" (7.6 cm) recessed shoulder for NSF7 units
- Display well 6 $\frac{5}{8}$ " (16.8 cm) deep
- Drain plug included
- Cold drop-ins are best used for holding periods up to 4 hours — for best performance, stainless steel containers are recommended



 [Go to VOLLRATH.com](http://VOLLRATH.com) for presentations about modular drop-in operation, features, and benefits



ITEM #	DESCRIPTION	OVERALL DIMENSIONS (L X W X H) IN (CM)	INTERIOR LENGTH IN (CM)	DISPLAY AREA IN (CM)	COM-PRESSOR	VOLTAGE	AMPS	PLUG
REFRIGERATED SHORT SIDE DROP-INS								
36652	Two-pan	45 $\frac{7}{8}$ x 18 $\frac{1}{8}$ x 22 $\frac{13}{16}$ (115.4 x 45.9 x 58)	40 $\frac{3}{4}$ (103.5)	40 $\frac{3}{4}$ x 11 $\frac{1}{8}$ (103.5 x 30.2)	$\frac{1}{2}$ hp	120	3.8	5-15P
36655	Three-pan	66 $\frac{7}{8}$ x 18 $\frac{1}{8}$ x 22 $\frac{13}{16}$ (170 x 45.9 x 58)	61 $\frac{1}{2}$ (156.2)	61 $\frac{1}{2}$ x 11 $\frac{1}{8}$ (156.2 x 30.2)	$\frac{1}{4}$ hp	120	4.9	5-15P
36658	Four-pan	88 $\frac{3}{8}$ x 18 $\frac{1}{8}$ x 22 $\frac{13}{16}$ (224.3 x 45.9 x 58)	82 $\frac{1}{4}$ (209)	82 $\frac{1}{4}$ x 11 $\frac{1}{8}$ (209 x 30.2)	$\frac{1}{4}$ hp	120	4.9	5-15P
NSF7 REFRIGERATED SHORT SIDE DROP-INS								
36653	Two-pan	45 $\frac{7}{8}$ x 18 $\frac{1}{8}$ x 22 $\frac{13}{16}$ (115.4 x 45.9 x 58)	40 $\frac{3}{4}$ (103.5)	40 $\frac{3}{4}$ x 11 $\frac{1}{8}$ (103.5 x 30.2)	$\frac{1}{4}$ hp	120	4.9	5-15P
36656	Three-pan	66 $\frac{7}{8}$ x 18 $\frac{1}{8}$ x 22 $\frac{13}{16}$ (170 x 45.9 x 58)	61 $\frac{1}{2}$ (156.2)	61 $\frac{1}{2}$ x 11 $\frac{1}{8}$ (156.2 x 30.2)	$\frac{1}{4}$ hp	120	4.9	5-15P
36659	Four-pan	88 $\frac{3}{8}$ x 18 $\frac{1}{8}$ x 22 $\frac{13}{16}$ (224.3 x 45.9 x 58)	82 $\frac{1}{4}$ (209)	82 $\frac{1}{4}$ x 11 $\frac{1}{8}$ (209 x 30.2)	$\frac{1}{2}$ hp	120	4.9	5-15P

Note: Modular Drop-Ins cannot be canceled or returned

Standard Refrigerated Cold Pan

- 8" (20.3 cm) deep well
- Thick polyurethane foam insulation
- Drain plug included
- Cold drop-ins are best used for holding periods up to 4 hours— for best performance, stainless steel containers are recommended



STANDARD ITEM #	REMOTE ITEM #**	DESCRIPTION	OVERALL DIMENSIONS IN (CM)	INTERIOR LENGTH IN (CM)	COMPRESSOR	VOLTAGE	AMPS	PLUG
36490	36490R	One-pan	15 x 26 (38.1 x 66)	12 (30.5)	$\frac{1}{2}$ hp	120	3.8	5-15P
36441	36441R	Two-pan	29 x 26 (73.7 x 66)	24 $\frac{3}{4}$ (62.9)	$\frac{1}{2}$ hp	120	3.8	5-15P
36442	36442R	Three-pan	41 $\frac{1}{2}$ x 26 (105.4 x 66)	37 $\frac{1}{2}$ (95.3)	$\frac{1}{2}$ hp	120	3.8	5-15P
36444	36444R	Four-pan	54 $\frac{3}{4}$ x 26 (139.1 x 66)	50 $\frac{1}{4}$ (127.6)	$\frac{1}{4}$ hp	120	4.9	5-15P
36446	36446R	Five-pan	68 x 26 (172.7 x 66)	63 (160)	$\frac{1}{4}$ hp	120	4.9	5-15P
36448	36448R	Six-pan	81 $\frac{1}{4}$ x 26 (206.4 x 66)	75 $\frac{3}{4}$ (192.4)	$\frac{1}{2}$ hp	120	7.2	5-20P

*With $\frac{7}{8}$ " (2.2 cm) corner radius

**Accessories available for remote installation. Remote units available but not shown; please reference spec sheet. Remote units do not include compressor

Note: Modular Drop-Ins cannot be canceled or returned