

NON-HEATED PATIENT TRAY DELIVERY CABINETS

Insulated – for 14"x18", 15"x20", or 10"x14" Size Patient Trays

NON-HEATED / INSULATED "ETC-1418-INS" SERIES


Reliable, quiet ride, all stainless steel patient tray delivery cabinet

- 1** Stainless steel tray racks hold a wide variety of trays including: 14"x18", 15"x20" and 10"x14"
- 2** Noise Suppression - FWE's patient tray delivery carts feature standard sound dampening components: latchless antimicrobial door handle and quiet ride multi-terrain casters
- 3** Transport - Even when fully loaded, these carts move with ease. Quiet ride multi-terrain casters mounted to stress plates absorb shock during room service delivery
- 4** Durability - Hospitals need durable foodservice equipment. FWE's food delivery carts take the abuse of any transport application. Standard features include: tubular welded stainless steel frame, full perimeter bumper, and heavy-duty push bar handles
- 5** Versatility - Serve hot and cold foods together using pellet systems, insulated or disposable containers - prepare meals ahead of time, then easily and quietly transport to serving location

****Two year limited warranty***



(Shown with Optional Accessory 3" Rack Spacings)



Stainless Steel Tray Racks



Antimicrobial Door Handle




Move with Ease



Full Perimeter Bumper

SPECIFICATIONS

NON-HEATED PATIENT TRAY DELIVERY CABINETS



CAPACITIES OF TRAYS / PANS: 5.25" (133mm) Spacings are Standard [A]							CONSULT FACTORY FOR SHIPPING CLASS		
MODEL NUMBER	TRAY CAPACITIES [A] @ 5.25" Spacings (133mm)			OVERALL EXTERIOR DIMENSIONS IN. (mm) (Height Includes Casters)			NO. OF DOORS	CASTER SIZE	SHIP WT. LBS. (KG)
	NUMBER OF 14"x18" or 15"x20" TRAYS AT SPACINGS OF:			HIGH "H"	DEEP "D"	WIDE "W"			
	3.0"	4.5"	5.25"[B]						
	16	11	9	61" (1550)	27" (686)	24" (610)	1	5"	255 (116)
	24	16	12	46" (1168)	27" (686)	43.75" (1112)	2	5"	350 (159)
	16	11	18	61.25" (1556)	27" (686)	43.75" (1112)	2	5"	395 (180)
	33	21	21	49" (1245)	27" (686)	63.75" (1620)	3	6"	480 (218)
	45	30	27	62" (1575)	27.5" (699)	63.75" (1620)	3	6"	565 (257)

[A] Rack accommodates:
(1) 14"x18", (1) 15"x20" or
(2) 10"x14" trays.

[B] Model numbers are based on
capacities @ spacings of 5.25".
Other spacings are available at
time of order.

ETC-1418-INS models are available with:
Pass-thru Door [add "P"]
See-thru Lexan Door [add "L"]

CONSTRUCTION. Heliarc welded, single unit construction of stainless steel; 20 gauge polished exterior, 22 gauge stainless steel interior with easy-to-clean covered corners. Welded tubular base frame shall be 1" square, heavy gauge stainless steel reinforcing plates at corners.

INSULATION. "Ultra-Guard" UG-26 high density fiberglass insulation throughout; top, back, bottom, sides, and door(s).

HANDLES. Heavy-duty push bar handles, solid formed 1" x .375" thick; mounted at each end of unit. Mountings reinforced with stainless steel channel.

BUMPER. Solid 1.5" wide continuous wraparound aluminum channel, bolted to frame, with snap-in, non-marking replaceable vinyl cushion. Full perimeter bumper extends beyond doors, handles, etc., for added protection. Shall be continuous, with corner cut-outs to facilitate cleaning.

DOORS AND LATCHES. Flush mounted, stainless steel insulated doors. High temperature gasket sealed; gasket shall be cabinet mounted. Each door shall have two (2) heavy-duty edgmount die cast hinges reinforced with stainless steel backing plates. Each door shall be equipped with a positive closing, flush-in-door, antimicrobial SaniGuard magnetic door handle.

CASTERS. Quiet ride multi-terrain casters in a configuration of two (2) rigid and two (2) swivel with brake. ETC-1418-21INS and ETC-1418-27INS are standard with a 6-Caster configuration of two (2) rigid and four (4) swivel with brake. Casters shall have a reinforced yoke mounted to 10 gauge caster plate. The caster mounting plate shall be secured to a 10 gauge stainless steel reinforcing stress plate via welded in place stainless steel studs. The reinforcing stress plates shall be welded to the heavy gauge tubular frame of the unit.

TRAY SLIDES. Unitized tray slide assemblies shall be heavy gauge stainless steel, channels fixed in place at 5.25" spacings. Assemblies are designed to accommodate one (1) 14"x18", one (1) 15"x20" or two (2) 10"x14" trays. Removable stainless steel tray racks shall easily lift off of heavy duty stainless steel supports without the use of tools. Racks with custom tray spacings are available at time of order (consult factory).
INSTALLATION. Unit should not be installed in an area where adverse environmental conditions are present.

DOORS

Key locking door latch
Paddle latch
Padlocking transport latch
Alternate door swing configurations

SPACINGS

Uprights with adjustable tray slides
(option available at no additional cost)

Custom tray rack spacing

CASTERS

All swivel (4 caster base only)
Larger casters
Floorlock (requires 6" casters)

EXTRAS

Security packages
X-Factor frame
Tubular stainless steel handles
Top bumper
Cold plate
Top guard rail
Menu card holder
Dry erase board
Grounding strap
Beverage urn angles